

Palvelu / Analyytti / Parametri	Service /Analysis	Menetelmä/Method
Vapaat harts- ja rasvahapot	Free rosin and fatty acids	Internal method, ASTM D 5974
Happoluku	Acid number	SCAN-T 11:72
Hartsihappopitoisuus	Rosin acids, total	SCAN-T 14:78
Jähmepiste	Pour point	SCAN-T 5:67/ASTM D97-17
Jodiluku	Iodine number	ASTM D 5768-02
Leimahduspiste	Flash point	ASTM D 93-10a
Pehmenemispiste hartsista	Softening point of rosin	ASTM D 6090-23
pH	pH	Internal method
Rikki	Sulphur	mod. ASTM D 4239
Saippuoitumaton aines	Unsaponifiable matter	SCAN-T 13:74
Saippuoitumisluku	Saponification value	SCAN-T12:72
Samenemispiste	Cloud point	ASTM D 2500:23
Suopaluku	Residual soap	PCTM 13:1996
Tiheys	Density	SCAN-T 2:65
Tuhka	Ash	SCAN-T 4:66/ASTM D 803-97
Väri, Gardner	Colour Gardner	ASTM D 6166:12
Vesi (KarlFischer)	Water (KarlFischer)	KF, ASTM D 890:12
Viskositeetti (Brookfield)	Viscosity (Brookfield)	ASTM D 2196:20
Kuiva-aine	Dry matter	SCAN 22:96, SCAN 22:77
Happoliuotus ja alkuainemääritys ICP-OES-tekniikalla	Acid digestion and measurement of elements, ICP-OES	Internal method HNO3-dig./ICP-OES
Tuhka	Ash	Internal method
Tärpättipitoisuus	Turpentine content	GC